

# PRODUCTS SERIES

## Biopek® MXP LP

### EXPANDABLE POLYSTYRENE

## TECHNICAL DATA SHEET

July 2025



#### Description Biopek® MXP LP

The product line Biopek® MXP LP is an expandable polystyrene foam (EPS) in spherical beads that is processed like standard EPS and has been designed to have an accelerated biodegradation compared to standard EPS, while maintaining the excellent performance characteristics of EPS molded foam.

Biopek® MXP LP products are compatible with many antistatic, color pigments and other additives that can be added during the transformation process.

#### Products and Applications

The Biopek® MXP LP series products are: **MXP240 LP**, **MXP340 LP**, **MXP440 LP**, and **MXP540 LP**. Biopek® MXP LP products can be used in a wide variety of applications including protective packaging, food packaging, fish boxes, coolers and nurseries. The typical use of each fraction is described in Table 1

#### Compliance with Standards and Regulations

Biopek® MXP LP foam manufactured from Biopek® MXP LP complies with the following standards and regulations according to its specific application:

- FDA Articles 21 CFR 177.1640 and 21 CFR 178.3010 for food contact packaging applications.
- NOM-010-STPS-2014 of the Mexican Legislation.
- EU 10-201 of the European Community for application as food contact packaging material.
- REACH Directive on the restriction of the use of hazardous substances.
- RoHS Directive restricting the use of heavy metals and specific flame retardants.

#### Packaging and Storage

Biopek® MXP LP products is available in flexible super-sacks 800 kgs (1,763 lbs). Internal plastic "Liners" are used to extend the life of the product by holding the blowing agent.

Biopek® MXP LP products should be stored in cool places (maximum temperature 27C / 80F), in their respective containers properly closed.

The typical shelf life of Biopek® MXP LP is 120 days from delivery date to the customer. Opened containers should be used as soon as possible, otherwise they should be hermetically sealed, otherwise their physical and/or chemical properties may change. Containers should be protected from rain, snow, frost, direct sunlight and physical damage.

#### Processing

Biopek® MXP LP based foams are produced in three main stages: pre-expansion, intermediate storage and molding. Full details of each of these three stages contact sales and technical service.

TABLE 1: APPLICATION

Products	Typical applications
Biopek® MXP240 LP	Blockmolding and packaging of high density, with excellent fusion and short cycle time, with characteristics of biodegradability in accelerated form.
Biopek® MXP340 LP	Molded packaging with excellent melting and short cycle time, with accelerated biodegradability characteristics.
Biopek® MXP440 LP	Narrow wall packaging molding (wall > 6mm), medium and high densities, with excellent superficial finish, good melt and excellent cycle time, with accelerated biodegradability characteristics.
Biopek® MXP540 LP	Cup molding and packaging of high density with excellent surface finish (wall > 3mm), with accelerated biodegradability characteristics

**Note:** These products can be used in other applications depending on the skill and equipment of each EPS Beads Customer.

# Styropek

www.styropek.com

Table 2: Product Technical Specifications

Products	Pentane, %	Monomer Resid, ppm	Size Range, mm	
Biopek® MXP240 LP	4.3 – 4.9	< 1000 ppm	0.85 - 1.70	96% min
Biopek® MXP340 LP	4.3 – 4.9	< 1000 ppm	0.60 - 1.18	97% min
Biopek® MXP440 LP	4.3 – 4.9	< 1000 ppm	<0.355	97.0% min 2.0% max
Biopek® MXP540 LP	4.3 – 4.9	< 1000 ppm	<0.30	96.0% min 3.0% max



### Pre-expansion

The minimum achievable density depends on the type of pre-expander and the technique used.

For proper processing, Biopek® MXP LP products should be processed in batch-type pre-expanders and can reach the densities shown in Table 3. In continuous pre-expanders, Biopek® MXP LP can be processed at densities greater than 28 kg/m<sup>3</sup> (1.75 lb/ft<sup>3</sup>).

TABLE 3 Typical densities

Products	Typical Density Range
Biopek® MXP240 LP	16 - 40 kg/m <sup>3</sup> - (1.00 – 2.5 lb/ft <sup>3</sup> )
Biopek® MXP340 LP	16 – 32 kg/m <sup>3</sup> - (1.00 – 2.0 lb/ft <sup>3</sup> )
Biopek® MXP440 LP	22 – 40 kg/m <sup>3</sup> - (1.37 – 2.5 lb/ft <sup>3</sup> )
Biopek® MXP540 LP	30 – 80 kg/m <sup>3</sup> - (1.87 – 5.0 lb/ft <sup>3</sup> )

lb/ft<sup>3</sup> = pound per cubic foot = pcf

The working vapor pressure in the pre-expander can be from 0.25 - 0.50 bar. Care should be taken during pre-expansion, as prolonged steam times can result in excessive pentane losses and difficulties in achieving adequate melts in the molding.

### Intermediate Storage

The recommended minimum intermediate storage time for these products is 2 hrs. depending on the density, temperature of the environment. Caution should be exercised when exceeding 24 hrs. as molding conditions can increase steam times and pressures to obtain acceptable melts.

### Molding

These products are designed for molding in automatic and manual machines, with or without vacuum. Molding can be achieved under a wide variety of conditions and densities. Molding vapor pressures are typically higher than that of regular pentane-containing Styropek® products.

### Safety Measure

It should be taken into consideration that during storage and processing of Biopek® MXP LP, flammable/explosive mixtures may be formed by the blowing agent (pentane), which migrates from the material. Therefore, all possible forms of ignition should be avoided (flames, sparks, electric shocks, static electricity build-up, etc.).

Adequate ventilation should be provided in all process areas to prevent the accumulation of pentane vapors.

For more safety information, please review the Safety Data Sheets (SDS) and for more details contact Sales and Technical Service.

### Biological Effects

None of its components is soluble in water. Biopek® MXP LP is a recyclable material, but please note that many jurisdictions prohibit the use of unqualified recycling claims if there is not an established program that actually collects, separates or

otherwise recovers a product or package from the waste stream where the product or package is sold.

Our claim is limited to the technical capability of our material to be recycled and does not apply to any final package or products. Customers must develop their own substantiation to support any recyclability or other environmental performance claims made for their entire product.

Subject to applicable local laws and regulations, expanded Biopek® MXP LP generally may be disposed of as non-hazardous waste.

### Biodegradability

This Biopek® MXP LP sample was tested using ASTM D5511 and demonstrated enhanced biodegradation of 64.7% in 1109 days using ASTM D5511 vs 0.9% biodegradation of standard EPS when tested under the same conditions for the same period of time.\*

\*Test conducted under laboratory conditions not necessarily reflective of actual product configurations or landfill conditions. Studies of other EPS formulations have shown increased degradation levels under longer laboratory conditions; we are continuing to test this product to assess if further degradation can be expected and will update our claims with new degradation rates, as they become available. California, Colorado (beginning January 2024), Maryland, Minnesota (beginning January 2026 for non-certified products), and Washington prohibit the sale of plastic packaging and plastic products that imply in any way that the item will break down, biodegrade, or decompose in a landfill or other environment.

For more detailed information regarding enhanced biodegradability of Biopek®, please refer to: [www.styropek.com](http://www.styropek.com)

### Chemical Effects

The resistance of Biopek® MXP LP to chemicals and solvents for more details contact Sales and Technical Service. Prolonged exposure to ultraviolet light causes the foamed material to turn yellowish and the surface to become brittle.

### REMARKS

**IMPORTANT:** The information contained in this publication is based on generally accepted technical procedures and on experience acquired by STYROPEK, and its technologists. Each transformer shall perform its own tests considering the specific factors of handling, processing, and application of Styropek®, and STYROPEK shall not be held responsible. of the variation of the materials used in each particular process. Likewise, it is the obligation of all those to whom STYROPEK supplies. with its products, to respect the industrial property rights of which STYROPEK is the owner.

**Styropek**

[www.styropek.com](http://www.styropek.com)